

REF . 4 016 79



## DISTRIBUTION CABINET XL<sup>3</sup> 125 - 4 ROWS - 72 MODULES - SURFACE MOUNTING



Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	48,944
Poids (g)	6 035,00

### Caractéristiques du produit

#### Surface mounting distribution cabinets

- Capacity 18 modules per row
- White RAL 9003
- Fully reversible cabinet (base, door and faceplates)
- Supplied with:
  - removable and pivoting chassis with rails fitted. Rails can be individually removed for easy cabling on site
  - removable cable entry plate (top and bottom)
  - removable faceplates (for each row)
  - IP 2X screw terminal blocks for neutral and earth
  - blanking plates (5 modules, separable per module or 1/2 module) 1 sheet of self-adhesive labels for circuit identification (marking per module)
- Spacing between rails 150 mm
- Adjustable rail (2-position) for fitting modular equipment or DPX<sup>3</sup> 160 moulded case circuit breakers
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products (2, 3 to 4-row cabinets)
- Doors to be ordered separately
- Number of rows : 4
- Number of modules : 72
- Height : 750 mm
- Width : 450 mm
- Depth : 128 mm

### Caractéristiques générales

#### Surface mounting cabinets XL<sup>3</sup> 125 - from 18 to 72 modules

- IP 40 - IK 09 with door
- IP 30 - IK 08 without door
- Class II
- Self-extinguishing: resistance to incandescent wire 650 °C
- Conform to IEC 60670-24
- Allows to achieve assemblies conform to IEC 61439-3

### Documentation associée

#### Catalogue pages & additional information

- [Description page \(p.222\)](#)
- [Technical page \(p.223\)](#)

#### Installation & technical data

- [F01233EN05](#)
- [EXB14055\\_WS\\_XL3125\\_EN](#)

#### Installation instructions & related documents

- [LE07398AA\\_01](#)

#### Agreements & certificates of conformity

- [OC / CB-654749](#)
- [LOVAG-IT 20](#)
- [OC / CB-675993](#)