

CAT. N° 4 017 04



## PRACTIBOX<sup>3</sup> FLUSH-MOUNTING CABINET WITH EARTH TERMINAL BLOCKS - TRANSPARENT DOOR - 3 ROWS - 12 MODULES PER ROW

Pack (number of units)	1
Volume (dm <sup>3</sup> )	25,166
Weight (g)	2 580,00

### Product characteristics

#### Flush-mounting distribution cabinets

- Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24)
- Supplied with:
  - removable chassis with rails fitted
  - reversible door (door + faceplate for 1-row cabinets)
  - removable faceplates for each row (for 2, 3 and 4-row cabinets)
  - IP 2X screw terminal blocks
  - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4-row cabinets)
- Spacing between rails 150 mm
- Door opening : 180°
- Can be equipped with lock and key n° 850 Cat.No 0 019 66

#### 8/12 modules per row with transparent door

- With earth terminal blocks
- Number of rows : 3
- Number of modules : 36
- Height : 522 mm
- Width : 304 mm
- Depth : 85 mm

### General characteristics

#### Flush-mounting cabinets Practibox<sup>3</sup> - from 8 to 72 modules

- Class II
- IP 40 - IK 07 with door
- Self-extinguishing: resistance to incandescent wire 850 °C
- Conform to IEC 60670-24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439-3

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.220\)](#)
- [Technical page \(p.221\)](#)



#### Installation & technical data

- [F01895EN-05](#)



#### Installation instructions & related documents

- [LE09548AA-01](#)



#### Agreements & certificates of conformity

- [OC / CB - IT-19045](#)