

CAT. N° 4 017 22



## HORIZONTAL PARTITION - FOR 2,3 OR 4 ROWS PRACTIBOX<sup>3</sup> CABINETS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,43
Weight (g)	65,00

### Product characteristics

#### Accessories

##### Horizontal partition for 18 modules per row cabinets

- For 2, 3 or 4-rows cabinets

### General characteristics

#### Flush-mounting cabinets Practibox<sup>3</sup> - from 8 to 72 modules

- Class II
- IP 40 - IK 07 with door
- Self-extinguishing: resistance to incandescent wire 850 °C
- Conform to IEC 60670-24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439-3

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.220\)](#)
- [Technical page \(p.221\)](#)



#### Installation instructions & related documents

- [LE06869AA](#)