

CAT. N° 4 017 51



PRACTIBOX³ FLUSH-MOUNTING CABINET WITH EARTH - NEUTRAL TERMINAL BLOCKS - TRANSPARENT DOOR - 1 ROW - 8 MODULES/ROW

Pack (number of units)	1
Volume (dm ³)	7,337
Weight (g)	826,00

Product characteristics

Flush-mounting distribution cabinets

- Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24)
- Supplied with:
 - removable chassis with rails fitted
 - reversible door (door + faceplate for 1-row cabinets)
 - removable faceplates for each row (for 2, 3 and 4-row cabinets)
 - IP 2X screw terminal blocks
 - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4-row cabinets)
- Spacing between rails 150 mm
- Door opening : 180°
- Can be equipped with lock and key n° 850 Cat.No 0 019 66

8/12 modules per row with transparent door

- With earth and neutral terminal blocks
- Number of rows : 1
- Number of modules : 8
- Height : 186 mm
- Width : 232 mm
- Depth : 80 mm

General characteristics

Flush-mounting cabinets Practibox³ - from 8 to 72 modules

- Class II
- IP 40 - IK 07 with door
- Self-extinguishing: resistance to incandescent wire 850 °C
- Conform to IEC 60670-24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439-3

Documentation



Catalogue pages & additional information

- [Description page \(p.220\)](#)
- [Technical page \(p.221\)](#)



Installation & technical data

- [F01895EN-05](#)



Installation instructions & related documents

- [LE09548AA-01](#)



Agreements & certificates of conformity

- [OC / CB-IT-19045](#)