

CAT. N° 4 017 59



## FLUSH-MOUNTING CABINET PRACTIBOX<sup>3</sup> -EARTH + NEUTRAL -TRANSPARENT DOOR -72 MODULES

Pack (number of units)	1
Volume (dm <sup>3</sup> )	52,116
Weight (g)	6 428,00

### Product characteristics

#### Flush-mounting distribution cabinets

- Box for masonry or dry partitions (with dry partitions kit Cat.No 4 017 24)
- Supplied with:
  - removable chassis with rails fitted
  - reversible door (door + faceplate for 1-row cabinets)
  - removable faceplates for each row (for 2, 3 and 4-row cabinets)
  - IP 2X screw terminal blocks
  - blanking plates (5 modules, separable per module or 1/2 module, for 2, 3 and 4-row cabinets)
- Spacing between rails 150 mm
- Door opening : 180°
- Can be equipped with lock and key n° 850 Cat.No 0 019 66

#### 18 modules per row with transparent door

- With earth and neutral terminal blocks
- Number of rows : 4
- Number of modules : 72
- Height : 756 mm
- Width : 436 mm
- Depth : 91 mm

### General characteristics

#### Flush-mounting cabinets Practibox<sup>3</sup> - from 8 to 72 modules

- Class II
- IP 40 - IK 07 with door
- Self-extinguishing: resistance to incandescent wire 850 °C
- Conform to IEC 60670-24 and IEC 62208 : allows to achieve assemblies conform to IEC 61439-3

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.220\)](#)
- [Technical page \(p.221\)](#)

#### Installation & technical data

- [F01895EN-03](#)
- [F01895EN-05](#)

#### Environmental product profile

- [LGRP-2015-204-V1-EN](#)

#### Installation instructions & related documents

- [LE06868AA](#)

#### Agreements & certificates of conformity

- [OC / CB-IT-19045](#)
- [LOVAG-IT18](#)