

CAT. N° 4 020 27


RCD RX³ - 2P 230 V~ - 80 A - 30 MA - AC TYPE

Pack (number of units)	1
Volume (dm ³)	0,369
Weight (g)	230,00

Product characteristics
2-pole - 230 V~
AC type

- Sensitivity : 30 mA
- In : 80 A
- Number of modules : 2

General characteristics
RCCBs RX³ - residual current circuit breakers from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Compatible with prong-type and fork type supply busbars
- Do not accept auxiliaries

Documentation

Catalogue pages & additional information

- [Description page \(p.050\)](#)
- [Dimensions of din-rail equipment](#)


Agreements & certificates of conformity

- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)
- [VDE - 40034493](#)
- [NF - NF012_1793](#)
- [VDE - 40034493](#)


Installation & technical data

- [F001535EN-03](#)