

CAT. N° 4 020 38



## RCD RX<sup>3</sup> - 2P 230 V~ - 63 A - 30 MA - A TYPE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	231,00

### Product characteristics

2-pole - 230 V~

#### A type

- Sensitivity : 30 mA
- In : 63 A
- Number of modules : 2

### General characteristics

#### RCCBs RX<sup>3</sup> - residual current circuit breakers from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Compatible with prong-type and fork type supply busbars
- Do not accept auxiliaries

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.050\)](#)
- [Dimensions of din-rail equipment](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)

#### Agreements & certificates of conformity

- [VDE - 40034495](#)
- [NF - NF012\\_1081](#)
- [VDE - 40034495](#)
- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)