

CAT. N° 4 030 01



## RCCB TX<sup>3</sup> - 2P 230 V~ - 30 MA - 40 A - AC TYPE - DO NOT ACCEPT AUXILIARIES

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,38
Weight (g)	212,00

### Product characteristics

2-pole - 230 V~

AC type

- Sensitivity : 30 mA
- In : 40 A
- Number of modules : 2

### General characteristics

**RCCBs TX<sup>3</sup> - residual current circuit breakers - from 25 A to 63 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)



#### Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)



#### Agreements & certificates of conformity

- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)
- [VDE - 40036431](#)
- [VDE - 40036431](#)