

CAT. N° 4 030 10



## RCCB TX<sup>3</sup> - 4P 400 V~ - 30 MA - 63 A - AC TYPE - NEUTRAL ON RIGHT-HAND - NO AUX

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,701
Weight (g)	374,00

### Product characteristics

#### 4-pole - 400 V~

- Neutral on left-hand side

#### AC type

- Sensitivity : 30 mA
- In : 63 A
- Number of modules : 4

### General characteristics

#### RCCBs TX<sup>3</sup> - residual current circuit breakers - from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [QC / CB - CB FR\\_705078](#)
- [QC / CB - CB-FR\\_700757](#)
- [VDE - 40036431](#)
- [VDE - 40036431](#)

#### Installation & technical data

- [F01543EN-01](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)