

CAT. N° 4 030 35

**RCCB TX<sup>3</sup> - 2P 230 V~ - 30 MA - 25 A - A TYPE - DO NOT ACCEPT AUXILIARIES**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,381
Weight (g)	196,00

**Product characteristics****2-pole - 230 V~****A type**

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 2

**General characteristics****RCCBs TX<sup>3</sup> - residual current circuit breakers - from 25 A to 63 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)

 **Agreements & certificates of conformity**

- [VDE - 40036430](#)
- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)
- [VDE - 40036430](#)