

CAT. N° 4 030 40



## RCCB TX<sup>3</sup> - 2P 230 V~ - 300 MA - 63 A - AC TYPE - DO NOT ACCEPT AUXILIARIES

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,367
Weight (g)	198,00

### Product characteristics

2-pole - 230 V~

AC type

- Sensitivity : 300 mA
- In : 63 A
- Number of modules : 2

### General characteristics

**RCCBs TX<sup>3</sup> - residual current circuit breakers - from 25 A to 63 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)
- [VDE - 40036431](#)
- [VDE - 40036431](#)

#### Installation & technical data

- [F01540EN-02](#)