

CAT. N° 4 030 42



RCCB TX³ - 4P 400 V~ - 300 MA - 25 A - AC TYPE - DO NOT ACCEPT AUXILIARIES

Pack (number of units)	1
Volume (dm ³)	0,701
Weight (g)	231,00

Product characteristics

4-pole - 400 V~

- Neutral on left-hand side

AC type

- Sensitivity : 300 mA
- In : 25 A
- Number of modules : 4

General characteristics

RCCBs TX³ - residual current circuit breakers - from 25 A to 63 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- Do not accept auxiliaries

Documentation

Catalogue pages & additional information

- [Description page \(p.053\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [QC / CB-CB FR_705078](#)
- [QC / CB-CB-FR_700757](#)
- [VDE-40036431](#)
- [VDE-40036431](#)

Installation & technical data

- [F01543EN-01](#)

Environmental product profile

- [LGRP-00366-V02](#)