

CAT. N° 4 041 54


MCB TX³ 10000 - 4P 400 V~ - 16 A - B CURVE


Pack (number of units)	1
Volume (dm ³)	0,716
Weight (g)	503,00

Product characteristics
4-pole 400 V~

- B curve
- Nominal rating I_n : 16 A
- Number of modules : 4

General characteristics
MCBs TX³ 10000 - thermal magnetic MCBs from 2 A to 63 A - B & C curve

- Conform to IEC 60898-1
- Compatible with prong-type and fork type supply busbars
- Equipped with special DIN rail clamp allowing independent MCB removal with supply busbar in place
- Breaking capacity:
 - 10000 - IEC 60898-1 - 230/400 V~
 - 10 kA - IEC 60947-2 - 230/400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Do not accept add-on modules

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.055\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [OC / CB-IT-21566](#)
- [VDE-40042812](#)

 **Installation & technical data**

- [F01900EN-01](#)

 **Environmental product profile**

- [LGRP-00763-V01](#)