

CAT. N° 4 065 35



## REMOTE TRIP HEAD ISOLATING SWITCH DX-IS - VISIBLE LOAD BREAK - 3P 400 V~ - 40 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,521
Weight (g)	283,00

### Product characteristics

#### Remote trip head isolating switches

- Red handle
- AC 22 A, AC 23 A
- Visible contact indication
- Remote tripping with associated control auxiliary
- Can be fitted with motorised controls and 2 DX<sup>3</sup> signalling auxiliaries
- Visual indication of the actual status of the contacts:
  - Closed position (red indicator)
  - Open position (green indicator)

#### 3P - 400 V~

- Compatible with prong-type and fork type supply busbars
- Nominal rating I<sub>n</sub> : 40 A
- Number of modules : 3

### General characteristics

#### Isolating switches DX<sup>3</sup>-IS - from 16 A to 125 A

- Double break contacts

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.056\)](#)
- [Technical page \(p.058\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [NF - 632428A](#)
- [OC / CB - 632428C](#)

#### Installation & technical data

- [F01677EN-00](#)