

CAT. N° 4 074 25


**MCB - DX<sup>3</sup> 6000 - 10 KA - 1P - 230/400 V~ - 1 A - B CURVE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,229
Weight (g)	147,00

**Product characteristics**
**Single pole 230/400 V~**

- B curve
- Nominal rating I<sub>n</sub> : 1 A
- Number of modules : 1

**General characteristics**
**MCBs DX<sup>3</sup> 6000 - 10 kA - thermal magnetic circuit breakers from 1 A to 63 A - B and C curves**

- Conform to IEC 60898-1
- Compatible with both, prong-type and fork type supply busbars
- Breaking capacity
  - 6000 - IEC 60898-1 - 400 V~
  - 10 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries, motorised controls and add-on modules

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.064\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Agreements & certificates of conformity**

- [OC / CB - IT-10651](#)
- [VDE - 40047508](#)
- [OC / CB - IT-10651/M1](#)
- [OC / CB - IT-18023](#)
- [VDE - 40034165](#)

 **Installation & technical data**

- [F01591EN-02](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0112A-FR](#)