

CAT. N° 4 074 29


MCB - DX³ 6000 - 10 KA - 1P - 230/400 V~ - 6 A - B CURVE

Pack (number of units)	10
Volume (dm ³)	1,619
Weight (g)	1 378,00

Product characteristics
Single pole 230/400 V~

- B curve
- Nominal rating I_n : 6 A
- Number of modules : 1

General characteristics
MCBs DX³ 6000 - 10 kA - thermal magnetic circuit breakers from 1 A to 63 A - B and C curves

- Conform to IEC 60898-1
- Compatible with both, prong-type and fork type supply busbars
- Breaking capacity
 - 6000 - IEC 60898-1 - 400 V~
 - 10 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation

Catalogue pages & additional information

- [Description page \(p.064\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Environmental product profile

- [Environnemental product sheet n°8 E0112A-FR](#)


Agreements & certificates of conformity

- [OC / CB - IT-10651](#)
- [VDE - 40047508](#)
- [OC / CB - IT-10651/M1](#)
- [OC / CB - IT-18023](#)
- [VDE - 40034165](#)