

CAT. N° 4 074 71


MCB - DX³ 6000 - 10 KA - 1P+N 230 V~ - 4 A - B CURVE

Pack (number of units)	1
Volume (dm ³)	0,207
Weight (g)	119,00

Product characteristics
Single pole + neutral 230 V~

- Neutral on right-hand side
- B curve
- Nominal rating I_n : 4 A
- Number of modules : 1

General characteristics
MCBs DX³ 6000 - 10 kA - thermal magnetic circuit breakers from 1 A to 63 A - B and C curves

- Conform to IEC 60898-1
- Compatible with both, prong-type and fork type supply busbars
- Breaking capacity
 - 6000 - IEC 60898-1 - 400 V~
 - 10 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.064\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Agreements & certificates of conformity**

- [VDE - 40043029](#)
- [QC / CB - 667184](#)

 **Installation & technical data**

- [F01441EN-01](#)