

CAT. N° 4 079 70


MCB - DX³ 6000 - 10 KA - 1P - 230/400 V~ - 13 A - D CURVE


Pack (number of units)	1
Volume (dm ³)	0,219
Weight (g)	152,00

Product characteristics
Single pole 230/400 V~

- D curve
- Nominal rating I_n : 13 A
- Number of modules : 1

General characteristics
MCBs DX³ 6000 - 10 kA - thermal magnetic MCBs from 0.5 A to 63 A - D curve

- Conform to IEC 60898-1
- Compatible with both prong-type and fork type supply busbars
- Breaking capacity:
 - 6000 - IEC 60898-1 - 400 V~
 - 10 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.065\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Agreements & certificates of conformity**

- [VDE - 40047508](#)
- [QC / CB - IT-10651](#)
- [QC / CB - IT-10651/M1](#)
- [QC / CB - IT-18023](#)
- [VDE - 40034165](#)

 **Installation & technical data**

- [F01591EN-03](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0112A-FR](#)