

CAT. N° 4 094 30

**MCB - DX³ 10000 - 16 KA - 1P - 230/400 V~ - 10 A - D CURVE**

Pack (number of units)	1
Volume (dm ³)	0,229
Weight (g)	141,00

Product characteristics**Single pole 230/400 V~**

- D curve
- Nominal rating I_n : 10 A
- Number of modules : 1

General characteristics**MCBs DX³ 10000 - 16 kA - thermal magnetic MCBs from 2 A to 125 A - D curve**

- Conform to IEC 60898-1
- Compatible with both prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)
- Breaking capacity:
 - 10000 - IEC 60898-1 - 400 V~
 - 16 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation**Catalogue pages & additional information**

- [Description page \(p.067\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

**Agreements & certificates of conformity**

- VDE - 40034176
- OC / CB - IT - 14353
- OC / CB - IT-10652/M2
- OC / CB - IT-10652/M1