

CAT. N° 4 095 26

**MCB - DX³ 10000 - 16 KA - 4P 400 V~ - 2 A - D CURVE**

Pack (number of units)	1
Volume (dm ³)	0,716
Weight (g)	554,00

Product characteristics**4-pole 400 V~**

- D curve
- Nominal rating I_n : 2 A
- Number of modules : 4

General characteristics**MCBs DX³ 10000 - 16 kA - thermal magnetic MCBs from 2 A to 125 A - D curve**

- Conform to IEC 60898-1
- Compatible with both prong-type and fork type supply busbars (except 80 A, 100 A and 125 A MCBs)
- Breaking capacity:
 - 10000 - IEC 60898-1 - 400 V~
 - 16 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries, motorised controls and add-on modules

Documentation **Catalogue pages & additional information**

- [Description page \(p.067\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Agreements & certificates of conformity**

- [VDE - 40034176](#)
- [QC / CB - IT - 14353](#)
- [QC / CB - IT-10652/M2](#)
- [QC / CB - IT-10652/M1](#)

 **Installation & technical data**

- [F01559EN-03](#)