

CAT. N° 4 095 71



MCB - DX³ - 16 KA - DIRECT CURRENT - 12 V= TO 500 V= - 2P - 32 A

Pack (number of units)	1
Volume (dm ³)	0,369
Weight (g)	302,00

Product characteristics

Direct current circuit breakers

- Nominal rating I_n : 32 A
- Number of poles protected : 2
- Number of modules : 2

General characteristics

MCBs DX³ - 16 kA - direct current - thermal magnetic circuit breakers from 0.5 A to 63 A

- Operating voltage from 12 V= to 500 V=
- Breaking capacity
 - 16 kA - IEC 60947-2 - 250 V=
 - 10 kA - IEC 60947-2 - 440 V=
 - 6 kA - IEC 60947-2 - 500 V=
- Magnetic threshold from 5 to 7 I_n
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation

Catalogue pages & additional information

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F01462EN-02](#)