

CAT. N° 4 097 63

**MCB - DX³ - 25 KA - 1P - 230/400 V~ - 100 A - C CURVE**


Pack (number of units)	1
Volume (dm ³)	0,332
Weight (g)	248,00

Product characteristics**Single pole 230/400 V~**

- C curve
- Nominal rating I_n : 100 A
- Number of modules : 1.5

General characteristics**MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
- 25 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation** Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 Installation & technical data

- [F01205EN-00](#)

 Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)
- [LGRP-00269-V01](#)

 Installation instructions & related documents

- [LE03603AG](#)

 Agreements & certificates of conformity

- [LOVAG-IT 12](#)