

CAT. N° 4 097 64


MCB - DX³ - 25 KA - 1P - 230/400 V~ - 125 A - C CURVE


Pack (number of units)	1
Volume (dm ³)	0,332
Weight (g)	252,00

Product characteristics
Single pole 230/400 V~

- C curve
- Nominal rating I_n : 125 A
- Number of modules : 1.5

General characteristics
MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves

- Breaking capacity:
- 25 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01205EN-00](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)
- [LGRP-00269-V01](#)

 **Installation instructions & related documents**

- [LE03603AG](#)

 **Agreements & certificates of conformity**

- [LOVAG-IT 12](#)