

CAT. N° 4 097 78

**MCB - DX³ - 25 KA - 3P 400 V~ - 2 A - C CURVE**

Pack (number of units)	1
Volume (dm ³)	0,716
Weight (g)	421,00

Product characteristics**3-pole - 400 V~**

- C curve
- Nominal rating I_n : 2 A
- Number of modules : 3

General characteristics**MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
 - 25 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation**Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

**Agreements & certificates of conformity**

- [LOVAG - IT 13.030](#)

**Installation & technical data**

- [F01303EN-00](#)