

CAT. N° 4 097 82


MCB - DX³ - 25 KA - 3P 400 V~ - 20 A - C CURVE

Pack (number of units)	1
Volume (dm ³)	0,716
Weight (g)	459,00

Product characteristics
3-pole - 400 V~

- C curve
- Nominal rating I_n : 20 A
- Number of modules : 3/4.5

General characteristics
MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves

- Breaking capacity:
 - 25 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Technical page \(p.074-075\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Agreements & certificates of conformity**

- [LOVAG-IT 13](#)

 **Installation & technical data**

- [F01303EN-00](#)