

CAT. N° 4 097 90


**MCB - DX<sup>3</sup> - 25 KA - 3P 400 V~ - 125 A - C CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	692,00

**Product characteristics**
**3-pole - 400 V~**

- C curve
- Nominal rating I<sub>n</sub> : 125 A
- Number of modules : 4.5

**General characteristics**
**MCBs DX<sup>3</sup> - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
- 25 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


**Agreements & certificates of conformity**

- [LOVAG - IT 12.013](#)


**Installation & technical data**

- [F01205EN-00](#)


**Environmental product profile**

- [Environnemental product sheet n°A E0084C-EN](#)
- [Environnemental product sheet n°20 E0084C-EN](#)