

CAT. N° 4 098 08


**MCB - DX<sup>3</sup> - 25 KA - 1P - 230/400 V~ - 20 A - D CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,332
Weight (g)	239,00

**Product characteristics**
**Single pole 230/400 V~**

- D curve
- Nominal rating I<sub>n</sub> : 20 A
- Number of modules : 1/1.5

**General characteristics**
**MCBs DX<sup>3</sup> - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves**

- Breaking capacity:
  - 25 kA - IEC 60947-2 - 400 V~
  - Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


**Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)


**Agreements & certificates of conformity**

- [LOVAG - IT 13.030](#)