

CAT. N° 4 098 33



## MCB - DX<sup>3</sup> - 25 KA - 3P 400 V~ - 16 A - D CURVE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	666,00

### Product characteristics

#### 3-pole - 400 V~

- D curve
- Nominal rating I<sub>n</sub> : 16 A
- Number of modules : 3/4.5

### General characteristics

#### MCBs DX<sup>3</sup> - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves

- Breaking capacity:
- 25 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F01217EN-01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E0084C-EN](#)
- [Environnemental product sheet n°20 E0084C-EN](#)

#### Installation instructions & related documents

- [LE03603AB](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 13.030](#)