

CAT. N° 4 098 46



MCB - DX³ - 25 KA - 4P 400 V~ - 16 A - D CURVE

Pack (number of units)	1
Volume (dm ³)	1,04
Weight (g)	872,00

Product characteristics

4-pole - 400 V~

- D curve
- Nominal rating I_n : 16 A
- Number of modules : 4 / 6

General characteristics

MCBs DX³ - 25 kA - thermal magnetic MCBs from 2 A to 125 A - C and D curves

- Breaking capacity:
- 25 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation

Catalogue pages & additional information

- [Description page \(p.068\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F01217EN-01](#)

Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)
- [LGRP-00269-V01](#)

Installation instructions & related documents

- [LE03603AG](#)

Agreements & certificates of conformity

- [LOVAG-IT 13](#)