

CAT. N° 4 100 14


**MCB - DX<sup>3</sup> - 36 KA - 2P - 230/400 V~ - 63 A - C CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,605
Weight (g)	462,00

**Product characteristics**
**2-pole - 230/400 V~**

- C curve
- Nominal rating I<sub>n</sub> : 63 A
- Number of modules : 3

**General characteristics**
**MCBs DX<sup>3</sup> - 36 kA - thermal magnetic MCBs from 10 A to 80 A - C curve**

- Breaking capacity:
- 36 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> auxiliaries and accessories

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


**Installation & technical data**

- [F01218EN-00](#)


**Environmental product profile**

- [Environnemental product sheet n°A E0084C-EN](#)
- [Environnemental product sheet n°20 E0084C-EN](#)


**Installation instructions & related documents**

- [LE03603AB](#)


**Agreements & certificates of conformity**

- [LOVAG - IT 13031](#)