

CAT. N° 4 100 34


**MCB - DX<sup>3</sup> - 36 KA - 4P 400 V~ - 16 A - C CURVE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	874,00

**Product characteristics**
**4-pole - 400 V~**

- C curve
- Nominal rating I<sub>n</sub> : 16 A
- Number of modules : 6

**General characteristics**
**MCBs DX<sup>3</sup> - 36 kA - thermal magnetic MCBs from 10 A to 80 A - C curve**

- Breaking capacity:
  - 36 kA - IEC 60947-2 - 400 V~
  - Can be equipped with DX<sup>3</sup> auxiliaries and accessories

**Documentation**
 **Catalogue pages & additional information**

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01218EN-00](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)

 **Installation instructions & related documents**

- [LE03603AG](#)

 **Agreements & certificates of conformity**

- [LOVAG - IT 13031](#)