

CAT. N° 4 101 37


MCB - DX³ - 50 KA - 1P - 230/400 V~ - 25 A - C CURVE

Pack (number of units)	1
Volume (dm ³)	0,332
Weight (g)	237,00

Product characteristics
Single pole 230/400 V~

- C curve
- Nominal rating I_n : 25 A
- Number of modules : 1.5

General characteristics
MCBs DX³ - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves

- Breaking capacity:
 - 50 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ auxiliaries and accessories

Documentation

Catalogue pages & additional information

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


Installation & technical data

- [F01220EN-01](#)


Environmental product profile

- [Environnemental product sheet n°8 E0084A-FR](#)


Installation instructions & related documents

- [LE03603AG](#)


Agreements & certificates of conformity

- [LOVAG - IT 14.021](#)