

CAT. N° 4 101 67



## MCB - DX<sup>3</sup> - 50 KA - 3P 400 V~ - 63 A - C CURVE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,04
Weight (g)	677,00

### Product characteristics

#### 3-pole - 400 V~

- C curve
- Nominal rating I<sub>n</sub> : 63 A
- Number of modules : 4.5

### General characteristics

#### MCBs DX<sup>3</sup> - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves

- Breaking capacity:
- 50 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX<sup>3</sup> auxiliaries and accessories

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.069\)](#)
- [Technical page \(p.074-075\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- [F01220EN-01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E0084C-EN](#)
- [Environnemental product sheet n°20 E0084C-EN](#)

#### Installation instructions & related documents

- [LE03603AB](#)

#### Agreements & certificates of conformity

- [LOVAG - IT 14.021](#)