

REF . 4 101 80


MCB - DX³ - 50 KA - 4P 400 V~ - 63 A - C CURVE



Emballage (nombre number of units)	1
Volume (dm ³)	1,04
Poids (g)	868,00

Caractéristiques du produit
4-pole - 400 V~

- C curve
- Nominal rating In : 63 A
- Number of modules : 6

Caractéristiques générales
MCBs DX³ - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves

- Breaking capacity:
- 50 kA - IEC 60947-2 - 400 V~
- Can be equipped with DX³ auxiliaries and accessories

Documentation associée
 **Catalogue pages & additional information**

- [Description page \(p.069\)](#)
- [Technical page \(p.074-075\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01220EN-01](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)
- [LGRP-00269-V01](#)

 **Installation instructions & related documents**

- [LE03603AG](#)

 **Agreements & certificates of conformity**

- [LOVAG-IT 14](#)