

CAT. N° 4 105 77



ADD-ON MODULES DX³ - 2P 230 V~ - 125 A - 30 MA - HPI TYPE - FOR 1.5 MODULES DX³ MCB

Pack (number of units)	1
Volume (dm ³)	3,124
Weight (g)	524,00

Product characteristics

2-pole - 230 V~

F type (old Hpi type)

- Sensitivity : 30 mA
- Nominal rating In : 125 A
- Number of modules : 4

General characteristics

Add-on modules DX³ - for 1.5 module/pole DX³ MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.Nos 4 106 57/58/59
- AC type : detect AC components faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1.5 module per pole DX³ MCBs

Documentation

Catalogue pages & additional information

- [Description page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F01206EN-04](#)

Installation instructions & related documents

- [LE03604ABDX3BDAHFPo](#)

Environmental product profile

- [Environnemental product sheet n°8 E0079A-FR](#)