

CAT. N° 4 106 24



## ADD-ON MODULES DX<sup>3</sup> - 4P 400 V~ - 125 A - 30 MA - AC TYPE - FOR 1.5 MODULES DX<sup>3</sup> MCB

Pack (number of units)	1
Volume (dm <sup>3</sup> )	4,869
Weight (g)	881,00

### Product characteristics

4-pole - 400 V~

#### AC Type

- Sensitivity : 30 mA
- Nominal rating I<sub>n</sub> : 125 A
- Number of modules : 6

### General characteristics

#### Add-on modules DX<sup>3</sup> - for 1.5 module/pole DX<sup>3</sup> MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.Nos 4 106 57/58/59
- AC type : detect AC components faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1.5 module per pole DX<sup>3</sup> MCBs

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

#### Installation & technical data

- F01206EN-04

#### Installation instructions & related documents

- [LE03604ABDX3BDAHFPo](#)

#### Environmental product profile

- Environnemental product sheet n°8 E0079A-FR