

CAT. N° 4 106 44



ADD-ON MODULES DX³ - 4P-400 V~ -125 A-300/1000 MA ADJUSTABLE -HPI TYPE -1.5 MODULES DX³ MCB

Pack (number of units)	1
Volume (dm ³)	4,869
Weight (g)	895,00

Product characteristics

4-pole - 400 V~

F type (old Hpi type) adjustable

- Sensitivity : from 300 to 1000 mA
- Nominal rating I_n : 125 A
- Number of modules : 6

General characteristics

Add-on modules DX³ - for 1.5 module/pole DX³ MCBs

- Conform to IEC 61009-1, IEC 62423 (F type)
- Voltage independent tripping except Cat.Nos 4 106 57/58/59
- AC type : detect AC components faults
- F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping
- Detection of high frequency fault currents
- For mounting on the right-hand side of 1.5 module per pole DX³ MCBs

Documentation

Catalogue pages & additional information

- [Description page \(p.071\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Installation & technical data

- [F01206EN-04](#)

Installation instructions & related documents

- [LE03604ABDX3BDAHFPo](#)

Environmental product profile

- [Environnemental product sheet n°8 E0079A-FR](#)