

REF . 4 110 48



**RCBO - DX³ 6000 -10 KA -1P+N-230 V~ -10 A -30 MA -A
TYPE -N RIGHT HAND**



Emballage (nombre number of units)	1
Volume (dm ³)	0,38
Poids (g)	240,00

Caractéristiques du produit

Single pole + neutral - 230 V~

- Neutral on right-hand side

A Type 30 mA

- C curve
- Nominal rating In : 10 A
- Number of modules : 2

Caractéristiques générales

RCBOs DX³ 6000 - 10 kA - residual current circuit breakers from 3 A to 63 A - AC, A and F types

- Conform to IEC 61009-1, IEC 62423 (F type)
- Compatible with prong-type and fork type supply busbars
- Voltage independent tripping
- Breaking capacity:
 - 6000 - IEC 61009-1 - 10 kA / IEC 60947-2 for single pole + neutral, 2 and 4-pole
- AC type : detect AC component faults
- A type : detect AC and DC component faults
- F type (High immunity) : detect AC and pulsating DC residual currents
- Enhanced immunity to unwanted tripping in disturbed environments
- Detection of high frequency fault currents
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation associée

Catalogue pages & additional information

- [Description page \(p.061\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

Agreements & certificates of conformity

- [QC / CB-CB_FR_700911](#)
- [NF-NF012_1151](#)

Installation & technical data

- [F01573EN-03](#)

Environmental product profile

- [LGRP-00748-V02](#)