

CAT. N° 4 111 32

**RCBO - DX<sup>3</sup> 6000 - 6 KA - 1P+N 230 V~ - 20 A - 30 MA - A TYPE - N LEFT HAND**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,279  |
| Weight (g)                | 146,00 |

**Product characteristics****Single pole + neutral - 230 V~**

- Neutral on left-hand side

**A Type 30 mA**

- C curve
- Nominal rating In : 20 A
- Number of modules : 1

**General characteristics****RCBOs DX<sup>3</sup> 6000 - 6 kA - residual current circuit breakers from 6 A to 32 A - A type**

- Conform to IEC 61009-1
- Compatible with prong-type supply busbars
- Voltage dependent tripping
- Breaking capacity:
  - 6000 - IEC 61009-1 - 6 kA / IEC 60947-2 for single pole + neutral
- A type : detect AC and DC component faults
- Enhanced immunity to unwanted tripping in disturbed environments
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

**Documentation****Catalogue pages & additional information**

- [Description page \(p.060\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

**Agreements & certificates of conformity**

- [CCC - 2017010307963924](#)
- [OC / CB - 689349/A1](#)