

CAT. N° 4 111 32


**RCBO - DX<sup>3</sup> 6000 - 6 KA - 1P+N 230 V~ - 20 A - 30 MA - A TYPE - N LEFT HAND**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,279
Weight (g)	146,00

**Product characteristics**
**Single pole + neutral - 230 V~**

- Neutral on left-hand side

**A Type 30 mA**

- C curve
- Nominal rating In : 20 A
- Number of modules : 1

**General characteristics**
**RCBOs DX<sup>3</sup> 6000 - 6 kA - residual current circuit breakers from 6 A to 32 A - A type**

- Conform to IEC 61009-1
- Compatible with prong-type supply busbars
- Voltage dependent tripping
- Breaking capacity:
  - 6000 - IEC 61009-1 - 6 kA / IEC 60947-2 for single pole + neutral
- A type : detect AC and DC component faults
- Enhanced immunity to unwanted tripping in disturbed environments
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.060\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)


**Installation & technical data**

- [F02071EN-01](#)


**Installation instructions & related documents**

- [LE09580AA](#)


**Agreements & certificates of conformity**

- [OC / CB-689349/A1](#)