

CAT. N° 4 111 34

**RCBO - DX³ 6000 - 6 KA - 1P+N 230 V~ - 32 A - 30 MA - A
TYPE - N LEFT HAND**

Pack (number of units)	1
Volume (dm ³)	0,259
Weight (g)	154,00

Product characteristics**Single pole + neutral - 230 V~**

- Neutral on left-hand side

A Type 30 mA

- C curve
- Nominal rating I_n : 32 A
- Number of modules : 1

General characteristics**RCBOs DX³ 6000 - 6 kA - residual current circuit
breakers from 6 A to 32 A - A type**

- Conform to IEC 61009-1
- Compatible with prong-type supply busbars
- Voltage dependent tripping
- Breaking capacity:
 - 6000 - IEC 61009-1 - 6 kA / IEC 60947-2 for single pole + neutral
- A type : detect AC and DC component faults
- Enhanced immunity to unwanted tripping in disturbed environments
- Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls

Documentation**Catalogue pages & additional information**

- [Description page \(p.060\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

**Agreements & certificates of conformity**

- [CCC - 2017010307963924](#)
- [OC / CB - 689349/A1](#)