

CAT. N° 4 115 02

**RCCB TX<sup>3</sup> - 2P 230 V~ - 10 MA - 16 A - AC TYPE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,39
Weight (g)	235,00

**Product characteristics****2-pole - 230 V~****AC type**

- Sensitivity : 10 mA
- In : 16 A
- Number of modules : 2

**General characteristics****RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40041193](#)
- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)
- [VDE - 40041193](#)

 **Installation & technical data**

- [F01575EN-03](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)
- [Environnemental product sheet n°8 E0013C-EN](#)