

REF . 4 115 09

**RCCB TX³ - 2P 230 V~ - 30 MA - 25 A - AC TYPE**

Emballage (nombre number of units)	1
Volume (dm ³)	0,39
Poids (g)	201,00

Caractéristiques du produit**2-pole - 230 V~****AC type**

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 2

Caractéristiques générales**RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation associée**Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Agreements & certificates of conformity**

- [OC / CB-FR_713498](#)
- [VDE-40041193](#)
- [VDE-40041193](#)

**Installation & technical data**

- [F01575EN-03](#)

**Environmental product profile**

- [LGRP-00366-V02](#)