

CAT. N° 4 115 30



RCCB TX³ - 2P 230 V~ - 300 MA - 40 A - AC TYPE

Pack (number of units)	1
Volume (dm ³)	0,39
Weight (g)	200,00

Product characteristics

2-pole - 230 V~

AC type

- Sensitivity : 300 mA
- In : 40 A
- Number of modules : 2

General characteristics

RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation

Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [VDE - 40041193](#)
- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)
- [VDE - 40041193](#)

Installation & technical data

- [F01575EN-03](#)

Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)