

CAT. N° 4 115 60



## RCCB TX<sup>3</sup> - 2P 230 V~ - 30 MA - 40 A - A TYPE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,39
Weight (g)	198,00

### Product characteristics

2-pole - 230 V~

A type

- Sensitivity : 30 mA
- In : 40 A
- Number of modules : 2

### General characteristics

RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- VDE - 40041196
- OC / CB - CB FR\_700536
- OC / CB - CB FR\_704741

#### Installation & technical data

- [F01575EN-03](#)

#### Environmental product profile

- [Environnemental product sheet n°8 E0013C-EN](#)