

CAT. N° 4 115 61

**RCCB TX<sup>3</sup> - 2P 230 V~ - 30 MA - 63 A - A TYPE**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,39   |
| Weight (g)                | 236,00 |

**Product characteristics****2-pole - 230 V~****A type**

- Sensitivity : 30 mA
- In : 63 A
- Number of modules : 2

**General characteristics****RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40041196](#)
- [OC / CB - CB FR\\_700536](#)
- [OC / CB - CB FR\\_704741](#)

 **Installation & technical data**

- [F01575EN-03](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)