

CAT. N° 4 115 62

**RCCB TX³ - 2P 230 V~ - 30 MA - 80 A - A TYPE**


Pack (number of units)	1
Volume (dm ³)	0,39
Weight (g)	233,00

Product characteristics**2-pole - 230 V~****A type**

- Sensitivity : 30 mA
- In : 80 A
- Number of modules : 2

General characteristics**RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation **Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

 **Agreements & certificates of conformity**

- [VDE - 40041196](#)
- [OC / CB - CB FR_700536](#)
- [OC / CB - CB FR_704741](#)

 **Installation & technical data**

- [F01575EN-03](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)