

CAT. N° 4 115 66



RCCB TX³ - 2P 230 V~ - 100 MA - 63 A - A TYPE

Pack (number of units)	1
Volume (dm ³)	0,39
Weight (g)	203,00

Product characteristics

2-pole - 230 V~

A type

- Sensitivity : 100 mA
- In : 63 A
- Number of modules : 2

General characteristics

RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

Documentation

Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [VDE-40041196](#)
- [QC / CB-FR_713498](#)

Installation & technical data

- [F01575EN-03](#)

Environmental product profile

- [LGRP-00366-V02](#)