

CAT. N° 4 117 18

**RCCB TX<sup>3</sup> - 4P 400 V~ - 100 MA - 40 A - AC TYPE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,701
Weight (g)	337,00

**Product characteristics****4-pole 400 V~**

- Neutral on right-hand side

**AC type**

- Sensitivity : 100 mA
- In : 40 A
- Number of modules : 2

**General characteristics****RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types**

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

**Documentation****Catalogue pages & additional information**

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

**Environmental product profile**

- [Environnemental product sheet n°8 E0013C-EN](#)

**Agreements & certificates of conformity**

- [OC / CB - CB FR\\_705078](#)
- [OC / CB - CB-FR\\_700757](#)
- [VDE - 40041193](#)
- [VDE - 40041193](#)