

CAT. N° 4 117 64



## RCCB TX<sup>3</sup> - 4P 400 V~ - 30 MA - 25 A - A TYPE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,701
Weight (g)	333,00

### Product characteristics

#### 4-pole 400 V~

- Neutral on right-hand side

#### A type

- Sensitivity : 30 mA
- In : 25 A
- Number of modules : 4

### General characteristics

#### RCCBs TX<sup>3</sup> residual current circuit breakers - from 16 A to 80 A - AC and A types

- Conform to IEC 61008-1
- Compatible with prong-type and fork type supply busbars
- AC type : detect AC component faults
- A type : detect AC and DC component faults

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.054\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [VDE-40041196](#)
- [OC / CB-CB\\_FR\\_705078](#)
- [OC / CB-CB\\_FR\\_700757](#)

#### Installation & technical data

- [F01576EN-03](#)

#### Environmental product profile

- [LGRP-00366-V02](#)